PROGRESS LIGHTING DESIGN**+SERIES**™

Project:	 	
Fixture Type:		
Location:		

Contact:

P400372-197 Pinellas

Pinellas Collection Six-Light White Plaster Contemporary Chandelier

Category: Chandeliers Finish: White Plaster (Hand Painted) Construction: Steel Housing Glass/Shade: Gloss Finish Opal Glass Cone



Diameter: 30 in Height: 11-1/4 in Overall Ht. W/Stem And Swivel: 58 in

Gloss Finish Opal Glass Cone Width: 4-1/2 in Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cETLus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
One 6", four 12" lengths of stem included		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs.	