

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P400373-197 Pinellas

Pinellas Collection 14.37 in. Eight-Light White Plaster Contemporary Chandelier

- Category:** Chandeliers
- Finish:** White Plaster (Hand Painted)
- Construction:** Steel Housing
- Glass/Shade:** Gloss Finish Opal Glass Cone



Diameter: 40 in
 Height: 14-3/8 in
 Overall Ht. W/Stem And Swivel: 58-1/2 in

Gloss Finish Opal Glass Cone
 Width: 4-1/2 in
 Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(8) Candelabra Base (E12) Socket	cETLus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth			