

Project:

Fixture Type:

Location:

Contact:

P400374-197 Pinellas

Pinellas Collection Six-Light White Plaster Contemporary Linear Light

Category: Island/Linear

Finish: White Plaster (Hand Painted)
Construction: Steel Housing

Glass/Shade: Gloss Finish Opal Glass Cone



Length: 50 in Width: 15-1/2 in Height: 11 in

Overall Ht. W/Stem And Swivel: 59-1/2 in

Gloss Finish Opal Glass Cone

Width: 4-1/2 in Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cETLus Dry Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
Two 6", eight 12" lengths of stem included		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable	
Canopy covers a standard 4" recessed outlet box: 19" W., 0.81" ht., 4.75" depth		bulbs.	