

Project:		
Fixture Type:		
Location:		
Contact:		

P400377-205 Lusail

Lusail Collection Thirteen-Light Soft Gold Luxe Industrial Chandelier

Category: Chandeliers Finish: Soft Gold (Painted) Construction: Steel Housing



Diameter: 48 in Height: 42 in

Overall Ht. W/Chain And Stem: 104-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	15 feet of wire supplied	(13) Candelabra Base (E12) Socket	cETLus Dry Location Listed
	120 VAC		1-year Limited Warranty
1/8 IP mounting plate for outlet box included	Lamp Type Incandescent: 60-watt MAX per socket		,
4 in of 9 Gauge chain supplied		LED: 12.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth			