

Project:

Fixture Type:

Location:

Contact:

P400378-009

Haas

Haas Collection Four Light Brushed Nickel Mid-Century Modern Chandelier

Category: Chandeliers
Finish: Brushed Nickel (Plated)
Construction: Steel Housing

Glass/Shade: Etched Opal Glass Round



Diameter: 50 in Height: 5-7/8 in

Overall Ht. W/Stem And Swivel: 60 in

Etched Opal Glass Round

Width: 6 in Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
One 6", four 12" lengths of stem included		LED: 12.5-watt MAX per socket	
		Dimmable to 10% brightness (See	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth		Dimming Notes)	

