

Project: Fixture Type: Location: Contact:

P400378-31M Haas

Haas Collection Four Light Matte Black Mid-Century Modern Chandelier

Category: Chandeliers Finish: Matte Black (Painted) Construction: Steel Housing

Glass/Shade: Etched Opal Glass Round



Diameter: 50 in

Height: 5-7/8 in Overall Ht. W/Stem And Swivel: 60 in

Etched Opal Glass Round

Width: 6 in Height: 5-1/2 in

	5 7 /			
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION	
Ceiling Stem	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cULus Dry Location Listed	
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty	
One 6", four 12" lengths of stem included		LED: 12.5-watt MAX per socket		
		Dimmable to 10% brightness (See		
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht . 5.12" depth		Dimming Notes)		

