

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

**P400380-009**  
**Cornett**

Cornett Collection Six-Light Brushed Nickel Contemporary Chandelier

**Category:** Chandeliers  
**Finish:** Brushed Nickel (Plated)  
**Construction:** Steel Housing  
**Glass/Shade:** Brushed Nickel, Painted White Inside Metal Cone



Diameter: 44-1/8 in  
Height: 23 in  
Overall Ht. W/Stem And Swivel: 79-1/2 in

Brushed Nickel, Painted White Inside Metal Cone  
Width: 2-1/2 in  
Height: 3-13/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(6) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type 15 W max LED	1-year Limited Warranty
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth			