

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____



P400389-31M Seville

Six-Light Chandelier

Category: Chandelier
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear w/ Vertical Flutes Glass Flat Round

Diameter: 27-7/8 in
 Height: 17-3/4 in
 Overall Ht. W/Chain And Stem: 81 in

Clear w/ Vertical Flutes Glass Flat Round
 Width: 7-7/16 in
 Height: 10 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 3 links of chain	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/4 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
4 in of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.81" ht., 5.12" depth			