

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400390-31M Seville

Nine-Light Chandelier

Category: Chandelier

Finish: Matte Black (Painted)

Construction: Steel Construction

Glass/Shade: Clear w/ Vertical Flutes Glass Flat Round



Diameter: 37-7/8 in

Height: 30 in

Overall Ht. W/Chain And Stem: 93 in

Clear w/ Vertical Flutes Glass Flat Round

Width: 8-1/4 in

Height: 11-13/16 in

Clear w/ Vertical Flutes Glass Flat Round

Width: 8-1/4

Height: 11-13/16

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 3 links of chain	10 feet of wire supplied	(9) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/4 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
4 in of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.81" ht., 5.12" depth			