

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P400391-205 Allegheny

Five-Light Chandelier

Category: Chandelier

Finish: Soft Gold (Painted), surrounding frame is Foundry Gold finish

Construction: Steel Construction



Diameter: 22 in
 Height: 25-3/8 in
 Overall Ht. W/Chain: 76-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling/Chain	10 feet of wire supplied	(5) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
48 in of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs	