

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P400391-31M Allegheny

Five-Light Chandelier

**Category:** Chandelier

**Finish:** Matte Black (Painted), surrounding frame is Iron Copper finish

**Construction:** Steel Construction



Diameter: 22 in  
Height: 25-3/8 in  
Overall Ht. W/Chain: 76-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling/Chain	10 feet of wire supplied	(5) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
48 in of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs	