

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400395-31M Tosca

Six-Light Chandelier

Category: Chandelier

Finish: Matte Black (Painted)

Construction: Steel Construction

Glass/Shade: Faux Alabaster Glass Cone



Diameter: 41 in
Height: 16-1/8 in
Overall Ht. W/Stem And Swivel: 72-1/2 in

Faux Alabaster Glass Cone
Width: 3-1/2 in
Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with Swivel	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 1" ht., 5.12" depth		Fully dimmable with dimmable bulbs	