

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400396-31M Tosca

Ten-Light Chandelier

Category: Island/Linear
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Faux Alabaster Glass Cone



Length: 50 in
Width: 13-3/4 in
Height: 8-3/4 in
Overall Ht. W/Stem And Swivel: 58-1/2 in

Faux Alabaster Glass Cone
Width: 3-1/2 in
Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with Swivel	10 feet of wire supplied	(10) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 10.87" W., 0.81" ht., 4.5" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	