

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P400400-009
Tanner

Three-Light Chandelier

Category: Chandelier
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched Glass Cone



Diameter: 16-5/8 in
 Height: 16-1/2 in (21-1/2 in when facing down)
 Overall Ht. W/Chain: 60-1/2 in

Etched Glass Cone
 Width: 4-5/8 in
 Height: 5-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	6 feet of wire supplied	(3) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
3 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth		Fully dimmable with dimmable bulbs	