

Project: \_\_\_\_\_  
 Fixture Type: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Contact: \_\_\_\_\_

**P400401-31M**  
**Tanner**

Five-Light Chandelier

**Category:** Chandelier  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Construction  
**Glass/Shade:** Etched Glass Cone



Diameter: 20-1/2 in  
 Height: 16-1/2 in (21-1/2 in when facing down)  
 Overall Ht. W/Chain: 60-1/2 in

Etched Glass Cone  
 Width: 4-5/8 in  
 Height: 5-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	6 feet of wire supplied	(5) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
3 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth		Fully dimmable with dimmable bulbs	