

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P400409-205 Allegheny

Twelve-Light Chandelier

Category: Chandelier

Finish: Soft Gold (Painted), surrounding frame is Foundry Gold finish

Construction: Steel Construction

Diameter: 42-7/8 in

Height: 48 in

Overall Ht. W/Chain: 111-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	(12) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
5 feet of 9 Gauge chain supplied with quick link		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth			