

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P400409-31M Allegheny

Twelve-Light Chandelier

Category: Chandelier
Finish: Matte Black (Painted), surrounding frame is Iron Copper finish
Construction: Steel Construction



Diameter: 42-7/8 in
 Height: 48 in
 Overall Ht. w/Chain: 111-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	(12) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
5 feet of 9 Gauge chain supplied with quick link		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth			