

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

P4008-09

Five Light

This simple, classic five-light chandelier is popular in the vintage farmhouse inspired designs. White candle covers complete the look.

Category: Chandeliers

Finish: Brushed Nickel (plated)
Construction: Steel construction
Glass: White candle sleeves



Diameter: 21" Height: 16-1/2"

Overall ht. w/chain: 90-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included Six feet 9 gauge chain supplied Canopy covers a standard 4" hexagonal recessed outlet box 5-1/8" dia.	Pre-wired 10 feet of wire supplied 120V	Quantity: 5 60W Candelabra Base Candelabra phenolic sockets	UL-CUL Dry location listed 1 year warranty Companion fixtures are available