



DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

## P4158-09

### Kensington

The casual, comfortable feel of the Kensington Collection is perfect for many interiors. Three-light chandelier features scrolled metalwork in a Brushed Nickel finish. Trumpet-shaped, slightly textured glass shades are complemented by a etched white swirl finish.

**Category:** Chandeliers

**Finish:** Brushed Nickel (plated)

**Construction:** Steel construction construction

**Glass:** Swirled etched glass trumpet shaped shades



**Diameter:** 18"

**Height:** 20-1/2"

**Overall ht. w/chain:** 96"

**Glass:** 6" dia.

**Height:** 5"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted  Mounting strap for outlet box included  Six feet 9 gauge chain supplied  Canopy covers a standard 4" hexagonal recessed outlet box	Pre-wired  15 feet of wire supplied  120V	Quantity: 3 100W Medium Base  Medium ceramic sockets	UL-CUL Dry location listed  1 year warranty  Companion Bath and Vanity, Ceiling Fans, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Wall bracket, fixtures are available