

Project:

Fixture Type:

Location:

Contact:

P4217-109

Drum Shade

Drum Shade Collection Five-Light Brushed Bronze White Fabric Shade New Traditional Chandelier Light

Category: Chandeliers

Finish: Brushed Bronze (Plated) **Construction:** Steel Construction

Glass/Shade: White Textured Fabric Shade



Length: 21-5/8 in Diameter: 21-5/8 in Height: 21-1/8 in

Overall Ht. W/Chain: 66-1/8 in

White Textured Fabric Shade

Length: 21-5/8 in Width: 21-5/8 in Height: 7 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(5) Candelabra Base (E12) Lamp Type	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
3.5 feet of 9 gauge chain supplied		·	
Canopy covers a standard 4" recessed outlet box: 5.31" W., 1" ht., 5.31" depth		Fully dimmable with dimmable bulbs.	