

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P4288-09

Kensington

The casual, comfortable feel of the Kensington Collection is perfect for many interiors. Nine-light, two-tier chandelier features scrolled metalwork in a Brushed Nickel finish. Trumpet-shaped, slightly textured glass shades are complemented by a etched white swirl finish.

Category: Chandeliers

Finish: Brushed Nickel (plated)

Construction: Steel construction construction

Glass: Swirled etched glass trumpet shaped shades



Diameter: 31-1/2"
Height: 32"
Overall ht. w/chain: 155"

Glass: 7" dia.
Height: 5-3/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included Six feet 9 gauge chain supplied Canopy covers a standard 4" hexagonal recessed outlet box	Pre-wired 15 feet of wire supplied 120V	Quantity: 9 100W Medium Base Medium ceramic sockets	UL-CUL Dry location listed 1 year warranty Companion Bath and Vanity, Ceiling Fans, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Wall bracket, fixtures are available