

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P4365-09

Trinity

Fifteen-light three-tier chandelier featuring soft angles, curving lines and etched glass shades. Gracefully exotic, the Trinity Collection offers classic sophistication for transitional interiors. Sculptural forms of metal and glass are enhanced by a classic finish. This transitional style can transform a room or your whole home with its charming versatility.

- Brushed Nickel finish.
- Etched glass shades with slight banding.
- Sophisticated style for interior design.
- Graceful, soft angles with curving lines.

Category: Chandeliers

Finish: Brushed Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Etched glass shades



Diameter: 43-3/4"
Height: 43-5/8"
Overall Ht. W/Chain: 167"

Glass
Width: 5-5/8"
Height: 6-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included Ten feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5.5" W., 1.375" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Fifteen 75w max. Medium Base E26 base ceramic sockets	UL-CUL Dry location listed 1 year warranty