

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P4434-09

Wisten

Three-light chandelier is characterized by its unique tulip-shaped glass shades and bold, sculptural design. Arching rectangular arms flow through the fixture and consist of strap accents. Downlight style, etched white glass brings out the beauty for this Brushed Nickel fixture while also providing ideal illumination. Wisten Collection can be used to update a single room or an entire home to create a designer coordinated look.

Category: Chandeliers

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass: Etched glass



Diameter: 13"
Height: 20-1/2"
Overall ht. w/chain: 95"

Glass: 4" dia.
Height: 5-1/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included Six feet 9 gauge chain supplied Canopy covers a standard 4" hexagonal recessed outlet box	Pre-wired 15 feet of wire supplied 120V	Quantity: 3 100W Medium Base Medium porcelain sockets	UL-CUL1 year warranty Companion fixtures are available