

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P4458-09

Alexa

Three-light chandelier features a pleasingly simple Brushed Nickel frame while visually interesting textured white linen glass are complemented by a crisp clear edge accent. Six feet of 9 gauge chain is supplied for ceiling chain mount. Create the sophisticated feel of modern, urban living in your home - no matter where you live.

- Brushed Nickel finish.
- Textured white linen glass with a crisp, clear edge accent strip.
- Vintage mid-century modern look.
- Six feet of 9 gauge chain is supplied for ceiling chain mount.

Category: Chandeliers

Finish: Brushed Nickel (plated)

Construction: Steel Construction

Glass/Shade: Etched Linen with clear edge glass shades



Diameter: 17"
Height: 19-5/8"
Overall Ht. W/Chain: 94-5/8"

Glass
Width: 4-1/16"
Height: 5-9/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included Six feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5" W., 0.75" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Three 100w max. Medium Base E26 base ceramic sockets	UL-CUL Dry location listed 1 year warranty