

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P4490-09

Joy

Gleeful simplicity defines this five-light chandelier from the Joy Collection. Refreshing and fashionable arcing forms of Brushed Nickel metal arms enhance the etched white fluted glass. Coordinating fixtures from this collection let you decorate an entire home with confidence and style. The unique construction comes with two six inch stems and one 72 inch chain to allow the fixture to hang straight and level at any height. For stem hanging fixtures one or two links of chain are still required.

Category: Chandeliers

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass: Etched white inside glass shades



Diameter: 24-1/8"

Height: 18-7/8"

Overall ht. w/chain or stem:
105"

Glass: 6" dia.

Height: 5"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain or stem mounted Mounting strap for outlet box included Six feet 9 gauge chain supplied Two 6" lengths of stem included Canopy covers a standard 4" hexagonal recessed outlet box	Threaded socket ring secures glass Pre-wired 12 feet of wire supplied 120V	Quantity: 5 100W Medium Base Medium ceramic sockets	UL-CUL Dry location listed 1 year warranty Companion Bath and Vanity, Chandelier, Hall and Foyer, Pendant, Wall bracket, fixtures are available