

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

P4492-20

Joy

Gleeful simplicity defines this nine-light, two-tier chandelier from the Joy Collection. Refreshing and fashionable arcing forms of Antique Bronze metal arms enhance the etched light umber glass. Coordinating fixtures from this collection let you decorate an entire home with confidence and style. Unique stem-hung construction carries the clean line all the way to the ceiling and, for sloped ceilings, six feet of 9 gauge chain is provided to allow the fixture to hang straight and level.

Category: Chandeliers

Finish: Antique Bronze (painted) **Construction:** Steel construction **Glass:** Etched light umber glass shades



Diameter: 28" Height: 27-3/4"

Overall ht. w/chain or stem:

114-3/8"

Glass: 6" dia. Height: 5"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain or stem mounted Mounting strap for outlet box included Six feet 9 gauge chain supplied Two 6" lengths of stem included Canopy covers a standard 4" hexagonal recessed outlet box	Threaded socket ring secures glass Pre-wired 15 feet of wire supplied 120V	Quantity: 9 100W Medium Base Medium ceramic sockets	UL-CUL Dry location listed 1 year warranty Companion Bath and Vanity, Chandelier, Hall and Foyer, Pendant, Wall bracket, fixtures are available