

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P4558-144

Spirit

The spirit of craftsmanship prevails with subtle forms. Light amber etched glass shades highlight galvanized metal construction. New pebbles finish offers refreshed look for interior areas.

Category: Chandeliers

Finish: Pebbles (painted)

Construction: Steel construction

Glass: Light Umber Etched glass shades



Width: 13-1/8"
Length: 36"
Height: 23-5/8"
Overall ht. w/stem: 89-1/2"

Glass: 13-1/8" dia.
Height: 5-1/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem mounted with 6 links of chain mounted Mounting strap for outlet box included Two pieces of 6 links 9 gauge chain supplied Two 6", eight 12" lengths of stem included Canopy covers a standard 4" hexagonal recessed outlet box 5-7/8" dia., 13/16" depth	Threaded socket ring secures glass Pre-wired 15 feet of wire supplied 120V	Quantity: 2 100W Medium Base Medium porcelain sockets	UL-CUL Dry location listed 1 year warranty Companion Bath and Vanity, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Sconce, fixtures are available