

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P4635-20 Inspire

Inspire Collection Five-Light Antique Bronze Off-White Linen Shade Traditional Chandelier Light

Category: Chandeliers
Finish: Antique Bronze (Painted)
Construction: Steel Construction
Glass/Shade: Off-white Linen Drum Shades



Diameter: 22-13/16 in
Height: 20 in
Overall Ht. W/Chain: 94-1/4 in

Off-white Linen Drum Shades
Width: 5-1/2 in
Height: 4-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	Prewired	(5) Candelabra Base (E12) sockets	UL-CUL Dry Location Listed
Mounting strap for outlet box included	10 feet of wire supplied	Lamp Type B	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V	Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
canopy covers a standard 4" recessed outlet box: 5.1875" W., 1.4375" ht., 5.1875" depth		Fully dimmable with dimmable bulbs.	