

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

P500072-109

Tinsley

Featuring soft angles and impressive sculptural curves, Tinsley is a refreshingly updated design for Luxe, Transitional and Traditional interiors. The frame is complemented by classic etched glass shades or open candle designs. Overscaled details found in Tinsley are ideal for welcoming guests and visitors in a foyer or entryway, as well as in luxe dining room or traditional living room settings.

- Tinsley is a refreshingly updated design for Luxe, Transitional and Traditional interiors
- Features soft angles and impressive sculptural curves
- Brushed Bronze finish
- The frame is complemented by classic etched glass shade
- Uses one 100-watt max. medium base bulbs (sold separately)
- Overscaled details found in Tinsley are ideal for welcoming guests and visitors in a foyer or entryway, as well as in luxe dining room or traditional living room settings
- Can be displayed singularly or in groupings of two or more in a variety of spaces

Category: Pendants

Finish: Brushed Bronze (painted)
Construction: Steel construction
Glass/Shade: Etched Glass diffuser



Diameter: 7-1/2" Height: 12-1/2"

Overall Ht. W/Stem: 80-1/2"

Glass

Width: 7-1/2" Height: 5"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Hanging mounted Mounting strap for outlet box included Six links of 9 gauge chain supplied One 6", four 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 5.5" W., 1" ht., 5.5" depth	10 feet of wire supplied 120 V	Quantity: One 100w max. medium E26 base	cULus Dry location listed 1 year limited warranty
3.5 VI., 1 He, 3.5 depart			