

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P500089-009

Fontayne

With updated designs that honor the charm of early American styling, Fontayne provides a timeless elegance to Rustic Farmhouse, Modern Farmhouse and Urban Industrial spaces. Impressive graphic elements take center stage, while candelabra lights highlight subtle curves. Dual tone finish combinations of Brushed Nickel with weathered gray accents

- Features updated designs that honor the charm of early American styling
- Dramatic circular frame offers a stylish perch for graceful candelabra lights
- Dual tone finish combination is Brushed Nickel with hand painted weathered gray accents
- Uses six 60 watt max. candelabra base lamps
- Fontayne provides a timeless elegance to Rustic Farmhouse, Modern Farmhouse and Urban Industrial spaces
- Progress Lighting Design Series, a collection offering fashionable styles and affordable luxury
- Can be displayed singularly or in groupings of two or more in a variety of spaces

Category: Pendants

Finish: Brushed Nickel (plated)

Construction: Steel construction



Square: 20"

Height: 32"

Overall Ht. W/Chain: 107-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Hanging mounted</p> <p>Mounting strap for outlet box included</p> <p>Six feet of 9 gauge chain supplied</p> <p>Canopy covers a standard 4" octagonal recessed outlet box</p> <p>5.125" W., 0.75" ht., 5.125" depth</p>	<p>15 feet of wire supplied</p> <p>120 V</p>	<p>Quantity:</p> <p>Six 60w max. candelabra</p> <p>E12 base</p>	<p>cETLus Dry location listed</p> <p>1 year limited warranty</p>