

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

P500122-104

Seneca

Set the mood for the evening with the gaze-grabbing glamour of the Seneca eight-light foyer. Captivating, Polished Nickel arms cascade down from the simple orb that crowns the fixture. Elegant candelabra lights congregate at the center, placed in a two-tiered design that washes beautiful light over the entryway, dining table, or kitchen island below. This entrancing piece will charm any modern farmhouse or luxe interior.



Diameter: 19-5/8"
Height: 32"
Overall Ht. W/Chain And Stem: 98"

- A breath-taking design for welcoming guests in an entryway or for providing light above a dining table or large kitchen island
- Eight elegant candelabra lights ornament the smooth fixture
- The simple, sophisticated design is composed of a spacious styling that seamlessly incorporates both rectangular and circular shapes
- Four sleek, curved arms cascade down from the simple orb crowning the refined fixture
- Finished in stunning Polished Nickel
- Clean, modern, open-cage design is ideal for modern farmhouse and luxe interiors
- Uses eight 60-watt max candelabra base bulbs, including the LED equivalents, that are sold separately
- Measures 19-5/8 in diameter X 32 in height, Overall height with stem is 98 in, wire 180 in
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

Category: Hall & Foyer

Finish: Polished Nickel (Plated)

Construction: Steel Construction

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain mounted Mounting Strap for outlet box included Six links of 9 gauge chain supplied One 6", four 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 4.75" W., 0.75" ht., 4.75" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Eight 60w max. Candelabra Base E12 base Phenolic sockets	cULus Dry location listed