



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500125-31M Clifton Heights

Clifton Heights Collection One-Light Modern Farmhouse Matte Black Etched Glass Mini-Pendant Light

Category: Pendants

Finish: Matte Black (Painted)

Construction: Steel Construction

Glass/Shade: Etched Glass Square/Rectangular



Square: 5-1/2 in
Height: 7-1/4 in
Overall Ht. W/Chain Or Stem: 73-1/2 in

Etched Glass Square/Rectangular
Width: 5-1/2 in
Height: 5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(1) Medium Base (E26) Lamp Type A19	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	1-year Limited Warranty
Six links of 9 Gauge chain supplied		Fully dimmable with dimmable bulbs	
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 4.75" W., 1.12" ht., 4.75" depth			