

Project:		
Fixture Type:		
Location:		
Contact:		

P500126-31M

Clifton Heights

Clifton Heights Collection Two-Light Modern Farmhouse Matte Black Etched Glass Inverted Pendant Light

Category: Pendants

Finish: Matte Black (Painted)
Construction: Steel Construction

Glass/Shade: Etched Glass Square/Rectangular



Square: 16 in Height: 24-1/2 in

Overall Ht. W/Chain: 99-1/2 in

Etched Glass Square/Rectangular

Width: 16 in Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION	
Ceiling Chain	15 feet of wire supplied	(2) Medium Base (E26) Lamp Type A19	cULus Dry Location Listed	
1/8 IP mounting plate for outlet box included	120 VAC 1-year Limited Warranty Incandescent: 100-watt MAX per socket			
6 feet of 9 Gauge chain supplied		LED: 17.5-watt MAX per socket		
Canopy covers a standard 4" recessed outlet box: 4.75" W., 1.12" ht., 4.75" depth		Fully dimmable with dimmable bulbs		