

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500135-104 Range

Range Collection One-Light Pendant

Category: Pendants

Finish: Polished Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Clear Seeded Glass Shade



Diameter: 13 in
Height: 13 in
Overall Ht. W/Chain And Stem: 79 in

Clear Seeded Glass Shade
Width: 10-1/4 in
Height: 9-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	Prewired	Quantity: one 60 W max. A-19 or LED equivalent	cULus Dry Location Listed
Mounting plate for outlet box included	10 feet of wire supplied	E26 base porcelain socket	1-year Limited Warranty
six links of 9 gauge chain supplied	120 V		
one 6", four 12" lengths of stem included			
canopy covers a standard 4" recessed outlet box: 4.875" W., 0.75" ht., 4.875" depth			