



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500149-31M Classic Dome Pendant

Classic Dome Collection One-Light Matte Black Transitional Pendant

Category: Pendants

Finish: Matte Black (Painted)

Construction: Steel Construction

Glass/Shade: Etched Glass Bowl



Diameter: 15 in
Height: 8-1/8 in
Overall Ht. W/Chain: 46 in

Etched Glass Bowl
Width: 15 in
Height: 5-9/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
3 feet of 9 Gauge chain supplied		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.875" ht., 5" depth		Fully dimmable with dimmable bulbs	