

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P500158-141

Gulliver

The eight-light foyer in the Gulliver Collection features arching and delicate details that curve to create an airy design. Dual toned frame color combinations in a Galvanized finish with antique white accents The hand painted wood grained texture finished to emulate weathered driftwood complements Rustic and Modern Farmhouse home decor, as well as Urban Industrial and Coastal interior settings.



Diameter: 21"

Height: 33-3/4"

Overall Ht. W/Chain: 108-1/2"

- Gulliver's deftly painted two-toned metal frame reads like a rustic wood finish
- The distinguished two-tiered eight-light foyer is ideal for tall foyers and also looks great in libraries, vaulted great rooms or as a pair in large dining rooms
- Its rustic styling is ideal for Coastal or Farmhouse spaces
- Galvanized Finish with banding that resembles sun-bleached wood
- Measures 21in diameter x 33 3/4in ht.
- Uses eight, 60-watt max candelabra bulbs or LED equivalent (sold separately) vintage bulbs are an option for a rustic look
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available

Category: Hall & Foyer

Finish: Galvanized Finish (painted)

Construction: Steel Construction

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting strap for outlet box included Six feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5.125" W., 5.125" ht., 0.875" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Eight 60w max. Candelabra Base E12 base phenolic sockets	cETLus Dry location listed 1 year warranty