

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P500165-143

Gresham

A display of substantial style in an eight-light foyer, Gresham Collection's frame was inspired by the elegance of traditional iron structures. Specific attention to forging details creates a distinctive collection for Transitional and Farmhouse interior spaces. Seeded glass shades and a Graphite finish pair together to complete the look.

- Graphite finishes and organic seeded-glass shades form the basis of this collection that channels traditional iron structures
- This eight-light foyer fixture greets visitors with a pleasing, open feel within its dramatic dark frame
- The double-decker fixture feels most at home in a traditional or farmhouse-style setting
- With hand-forged details, the dark graphite frame makes this light a dramatic focal point
- Measures 24in diameter x 41 1/4in ht.
- Includes stacked cluster candelabras of 4 candelabra base lamps on each level with seeded-glass shades
- Uses eight, 60-watt max. candelabra base bulbs including LED equivalent (sold separately)
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available



Diameter: 24"
Height: 41-3/8"
Overall Ht. W/Chain: 115-1/2"

Width: 3-1/8"
Height: 5-7/8"

Category: Hall & Foyer

Finish: Graphite (painted)

Construction: Steel Construction

Glass/Shade: Clear Seeded glass Shades

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting U-channel mounting bar for outlet box included Six feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5" W., 0.8125" ht., 5" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Eight 60w max. Candelabra Base E12 base phenolic sockets	cULus Dry location listed 1 year warranty