

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

P500196-081

Point Dume™ - Shearwater

The Shearwater hanging lanterns embody Jeffrey's love of easy coastal living. His lighter lantern option combine Antique Nickel with clear glass and a soft-beige stitched leather handle. This family of fixtures is part of Jeffrey Alan Marks Point Dume™ lighting collection which celebrates a curated mix of yesterday and today, distilling both industrial and artisanal influences.

Category: Pendants

Finish: Antique Nickel (plated)

Construction: Steel Construction

Glass/Shade: Clear glass Flat Square/Rectangular



Width: 16-1/4" Height: 32" Depth: 16-1/4"

Overall Ht. W/Chain: 109"

Glass
Width: 12"
Height: 6-3/4"
Glass 2
Width: 15-3/8"
Length: 0-3/16"
Height: 20-3/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included Six feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5.875" W., 0.875" ht., 5.875" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Four 60w max. Candelabra Base E12 base Phenolic sockets	cCSAus Dry location listed 1 year warranty