

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500207-031 Bowman

Beautiful lighting will appeal to both your classic taste and your artistic spirit with the Bowman Collection Four-Light Black Pendant. Wandering eyes will focus on the clear, chiseled glass shade that encircles four elegant light sources gathering quietly at the light fixture's center. Handsome, black light bases with sophisticated curved arms originate from a decorative black knob that embellishes the outer bottom of the textured glass shade.

- Wandering eyes will focus on the clear, chiseled glass shade that encircles the elegant light sources gathering quietly at the light fixture's center.
- From the bottom of the sleek center column, a light base appears to gracefully drip down and provide an extra touch of refined visual interest.
- Smooth metal bars coated in a gorgeous galvanized finish curve to form a simple, open-cage fixture.
- Ideal for any foyer, dining room, or kitchen.
- A sophisticated choice for luxury, modern, and transitional interiors.
- Measures 14-1/4-inch width by 26-1/4-inch height.
- Uses four candelabra base bulbs that are sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Hall & Foyer

Finish: Matte Black (Painted)

Construction: Steel Construction

Glass/Shade: Clear Chiseled glass bell shaped shade



Diameter: 14-1/4 in
Height: 26-1/4 in
Overall Ht. W/Chain: 100-1/2 in

Clear Chiseled glass bell shaped shade
Width: 13-7/8 in
Height: 13-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity:	CULus Dry Location Listed
1/8 IP mounting plate for outlet box included	15 feet of wire supplied	Four 60 W max. Candelabra Base or LED equivalent	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V	E12 base Phenolic sockets	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth			