

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500208-009

Lassiter

Manifest a swoon-worthy lighting experience with the stunning blend of modern and traditional styles in this one-of-a-kind mini-pendant. Square tubing with clean, sharp angles is coated in a beautiful brushed nickel finish that demands your attention. A striking vintage light socket boasts its bold yet simple demeanor as it is encased in a clear glass shade to complete this statement-making light fixture.

- Square tubing with clean, sharp angles is coated in a beautiful brushed nickel finish that demands your attention.
- A striking vintage light socket boasts its bold yet simple demeanor as it is encased in a clear glass shade to complete this statement-making light fixture.
- Manifest a swoon-worthy lighting experience with the stunning blend of modern and traditional styles in this one-of-a-kind mini-pendant.
- Ideal for any foyer, kitchen, or dining room.
- Perfect for modern, new traditional, or contemporary settings.
- Measures 6-3/8-inch width by 12-1/2-inch height.
- Uses one medium base bulb that is sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Pendants

Finish: Brushed Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Clear glass Cylindrical Shade,



Diameter: 6-3/8 in
Height: 12-1/2 in
Overall Ht. W/Chain: 81 in

Clear glass Cylindrical Shade
Width: 6-5/16 in
Height: 6-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with 6 links of chain mounted	Prewired	Quantity:	CULus Dry Location Listed
Mounting plate for outlet box included	120 in of wire supplied	One 60 W max. Medium Base or LED equivalent	1-year Limited Warranty
Six links of 9 gauge chain supplied	120 V	E26 base Porcelain socket	
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 5.5 in W., 1.125 in ht., 5.2 in depth			