

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P500209-009 Lassiter

Manifest a swoon-worthy lighting experience with the stunning blend of the modern and traditional styles in this one-of-a-kind Lassiter Collection Three-Light Brushed Nickel Foyer. Square tubing with clean, sharp angles is coated in a beautiful brushed nickel finish that demands your attention. Striking vintage light sockets boast their bold yet simple demeanor as they hold clear glass shades to complete this statement-making light fixture.

- Coated in a beautiful brushed nickel finish.
- Square tubing with clean, sharp angles.
- Striking vintage light sockets demand your attention.
- Clear glass shades complete the blend of modern and traditional styles.
- Ideal for any foyer, kitchen, or dining room.
- Measures 16-5/8-inch width by 26-inch height.
- Perfect for modern, new traditional, or contemporary settings.
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

**Category:** Hall & Foyer

**Finish:** Brushed Nickel (Plated)

**Construction:** Steel Construction

**Glass/Shade:** Clear glass Cylindrical Shade



Diameter: 16-5/8 in  
Height: 26 in  
Overall Ht. W/Chain: 101 in

Clear glass Cylindrical Shade  
Width: 4 in  
Height: 7 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	Prewired	Quantity: Three 60 W max. Medium Base or LED equivalent	CULus Dry Location Listed
Mounting plate for outlet box included	15 feet of wire supplied	E26 base Porcelain sockets	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V		
Canopy covers a standard 4" recessed outlet box: 5.5" W., 1.125" ht., 5.5" depth			