

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500210-009

Durrell

This versatile foyer light from the Durrell Collection will easily find a home in a variety of settings in need of generous illumination. An elongated, open-cage frame coated in a farmhouse-style brushed nickel finish adds visual height to the design. Inside the frame gathers light bases on gently curved arms ready to emit a friendly glow. At the light fixture's center is a graceful wooden column coated in a ceruse white finish.

- An elongated, open-cage frame coated in a farmhouse-style brushed nickel finish adds visual height to the design.
- Inside the frame gathers light bases on gently curved arms ready to emit a friendly glow.
- A graceful wooden column at the light fixture's center is coated in a ceruse white finish.
- Ideal for any foyer, dining room, or kitchen.
- Perfect for rustic, farmhouse, and coastal settings.
- Measures 18-inch width by 28-1/2-inch height.
- Uses four candelabra base bulbs that are sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Hall & Foyer

Finish: Brushed Nickel (Plated)

Construction: Steel Construction



Diameter: 18 in
Height: 28-1/2 in
Overall Ht. W/Chain: 103-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity:	CULus Dry Location Listed
Mounting plate for outlet box included	15 feet of wire supplied	Four 60 W max. Candelabra Base or LED equivalent	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V	E12 base Phenolic sockets	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth			