

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P500212-009 Medal

Inspired by vintage automobile engines, this pendant boasts a signature star motif for added industrial character. The smooth metal shade is coated in a beautiful brushed nickel finish. The shade holds a prismatic glass diffuser primed for providing optimal task lighting.

- Inspired by vintage automobile engines, this pendant boasts a signature star motif for added industrial character.
- The smooth metal shade is coated in a beautiful brushed nickel finish.
- The shade holds a prismatic glass diffuser primed for providing optimal task lighting.
- Ideal for any foyer, kitchen, or dining room.
- Perfect for urban industrial, farmhouse, coastal, or vintage electric settings.
- Measures 17-3/8-inch width by 17-5/8-inch height.
- Uses one medium base bulb that is sold separately (100w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

**Category:** Pendants

**Finish:** Brushed Nickel (Plated)

**Construction:** Steel Construction

**Glass/Shade:** Clear Patterned glass lens



Diameter: 17-3/8 in  
Height: 17-5/8 in  
Overall Ht. W/Chain: 93 in

Clear Patterned glass lens  
Width: 15-1/4 in  
Height: 1-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity:	CULus Dry Location Listed
Mounting plate for outlet box included	10 feet of wire supplied	One 100 W max. Medium Base or LED equivalent	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 5.125" W., 0.8125" ht., 5.125" depth			