

Project:			
Fixture Type:			
Location:			
Contact:			

P500212-164

Medal

Inspired by vintage automobile engines, this pendant boasts a signature star motif for added industrial character. The smooth metal shade is coated in a beautiful coastal blue finish. The shade holds a prismatic glass diffuser primed for providing optimal task lighting.

- Inspired by vintage automobile engines, this pendant boasts a signature star motif for added industrial character.
- · The smooth metal shade is coated in a beautiful coastal blue finish.
- The shade holds a prismatic glass diffuser primed for providing optimal task lighting.
- · Ideal for any foyer, kitchen, or dining room.
- Perfect for urban industrial, farmhouse, coastal, or vintage electric settings.
- Measures 17-3/8-inch width by 17-5/8-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Pendants

Finish: Coastal Blue (Painted)
Construction: Steel Construction
Glass/Shade: Clear Patterned glass lens



Diameter: 17-3/8 in Height: 17-5/8 in

Overall Ht. W/Chain: 93 in

Clear Patterned glass lens Width: 15-1/4 in

Height: 1-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: One 100 W max. Medium Base or	CULus Dry Location Listed
Mounting plate for outlet box included	10 feet of wire supplied	LED equivalent	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 5.125" W., 0.8125" ht., 5.125" depth			