PROGRESS LIGHTING[™]

Project: Fixture Type:

Location:

Contact:

P500213-009 Parkhurst

Offer a modern spin on a timeless design with the Parkhurst Collection. Lantern-style metal frames create an airy structure ideal for emitting ambient light over memories being made below. Inside the frame perch smooth, simple light bases ready to offer your home a lovely glow.

- An open-cage metal frame creates a sophisticated, airy structure.
- A beautiful brushed nickel finish coats the lantern-style frame for an eye-pleasing, handsome design.
- Inside the frame perch smooth, simple light bases ready to offer your home a lovely glow.
- $\boldsymbol{\cdot}\,$ Ideal for a hallway, foyer, entryway, kitchen, or dining room.
- $\cdot\,$ Perfect for transitional, new traditional, and farmhouse settings.
- Measures 10-7/8-inch width by 19-3/4-inch height.
- Uses three candelabra base bulbs that are sold separately (60w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Hall & Foyer Finish: Brushed Nickel (Plated) Construction: Steel Construction



Square: 10-7/8 in Height: 19-3/4 in Overall Ht. W/Chain: 94 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Three 60 W max. Candelabra	CULus Dry Location Listed
Mounting plate for outlet box included	10 feet of wire supplied	Base or LED equivalent	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V	E12 base Phenolic sockets	

Canopy covers a standard 4" recessed outlet box: 5.6875" W., 0.9375" ht., 5.6875" depth