## **PROGRESS** LIGHTING<sup>™</sup>

Project:			
Fixture Type:			
Location:			

Contact:

## P500214-031 Parkhurst

Offer a modern spin on a timeless design with the Parkhurst Collection. Lantern-style metal frames create an airy structure ideal for emitting ambient light over memories being made below. Inside the frame perch smooth, simple light bases ready to offer your home a lovely glow.

- An open-cage metal frame creates a sophisticated, airy structure.
- A beautiful black finish coats the lantern-style frame for an eye-pleasing, handsome design.
- Inside the frame perch smooth, simple light bases ready to offer your home a lovely glow.
- Ideal for a hallway, foyer, entryway, kitchen, or dining room.
- · Perfect for transitional, new traditional, and farmhouse settings.
- Measures 14-3/8-inch width by 24-3/8-inch height.
- Uses four candelabra base bulbs that are sold separately (60w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Hall & Foyer Finish: Matte Black (Painted) Construction: Steel Construction



Square: 14-3/8 in Height: 24-3/8 in Overall Ht. W/Chain: 99-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Four 60 W max. Candelabra Base	CULus Dry Location Listed
Mounting plate for outlet box included	10 feet of wire supplied	or LED equivalent	1-year Limited Warranty
	120 V	E12 base Phenolic sockets	
6 feet of 9 gauge chain supplied			

Canopy covers a standard 4" recessed outlet box: 5.6875" W., 0.9375" ht., 5.6875" depth