

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P500225-031

### Bonn

The Bonn Collection Six-Light Black Pendant personifies an industrial vintage vibe sure to create an unforgettable lighting experience. Smooth metal bars coated in a beautiful matte black finish curve to form a simple, open-cage light fixture. From the bottom of the sleek center stem, light bases appear to gracefully drip down and give an extra touch of refined visual interest with their varying lengths.

- From the bottom of the sleek center column, light bases appear to gracefully drip down and provide an extra touch of refined visual interest with their varying lengths.
- Smooth metal bars curve to form a simple, open-cage design.
- The pendant is coated in a beautiful matte black finish for a classic look.
- Ideal for any foyer, dining room, or kitchen.
- A great vintage choice for urban industrial, vintage, electric, farmhouse, and rustic interiors.
- Measures 22-inch width by 23-1/8-inch height.
- Uses six medium base bulbs or vintage T10 bulbs that are sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

**Category:** Pendants

**Finish:** Matte Black (Painted)

**Construction:** Steel Construction



Diameter: 22 in  
Height: 23-1/8 in  
Overall Ht. W/Chain: 90 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with 6 links of chain mounted	Prewired	Quantity:	CETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	15 feet of wire supplied	Six 60 W max. Medium Base or LED equivalent	1-year Limited Warranty
Six links of 9 gauge chain supplied	120 V	E26 base Porcelain sockets	
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 5.125" W., 0.8125" ht., 5.125" depth			