

Project:			
Fixture Type:			
Location:			
Contact:			

P500227-141

Galveston

Create a countrified home that will make any guest want to stay for a cozy cup of tea and a warm slice of apple pie with this pendant. The clear seeded glass shades create a rustic atmosphere that is all about comfort and charm. The galvanized finish is inspired by modern farmhouse-style decor.

- The clear seeded glass shades create a rustic atmosphere that is all about comfort and charm.
- The galvanized finish is inspired by modern farmhouse-style decor.
- Create a countrified home that will make any guest want to stay for a cozy cup of tea and a warm slice of apple pie with this pendant.
- · Ideal for any foyer, entryway, patio, or porch.
- · Perfect for rustic and farmhouse settings.
- · Measures 17-3/4-inch width by 18-7/8-inch height.
- Uses three medium base bulbs that are sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Pendants

Finish: Galvanized Finish (Painted) **Construction:** Steel Construction

Glass/Shade: Clear Seeded glass Cylindrical Shade



Diameter: 17-3/4 in Height: 18-7/8 in

Overall Ht. W/Chain: 94 in

Clear Seeded glass Cylindrical Shade

Width: 2-1/4 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Three 60 W max. Candelabra	CETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	10 feet of wire supplied	Base or LED equivalent	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V	E12 base Phenolic sockets	
Canopy covers a standard 4" recessed outlet box: 5.125" W., 0.75" ht., 5.125" depth			