

Project:			
Fixture Type:			
Location:			
Cantasti			

## P500237-009

## **Passage**

Create a simply beautiful lighting experience in the heart of your home with the understated elegance of the Passage Collection. Smooth, thin metal arms reach down to hold a metal rim topping a simple, clear seeded glass shade that provides a dash of unexpected but pleasing visual texture for settings in need of an intimate, personal touch.

- A clear seeded glass shade provides a dash of unexpected but pleasing visual texture.
- A beautiful brushed nickel finish coats smooth metal arms as they reach down to hold a metal rim topping the glass shade.
- Three sleek light bases gather quietly at the center of the fixture.
- · Ideal for a hallway, foyer, kitchen, or dining room.
- Perfect for transitional, new traditional, and farmhouse settings.
- · Measures 12-inch width by 26-3/4-inch height.
- Uses three candelabra base bulbs that are sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Pendants

**Finish:** Brushed Nickel (Plated) **Construction:** Steel Construction

Glass/Shade: Clear Seeded glass Round Shade



Diameter: 12 in Height: 26-3/4 in

Overall Ht. W/Chain: 102 in

Clear Seeded glass Round Shade

Width: 12 in Height: 15-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Three 60 W max. Candelabra	CULus Dry Location Listed
1/8 IP mounting plate for outlet box included	15 feet of wire supplied	Base or LED equivalent	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V	E12 base Phenolic sockets	
Canopy covers a standard 4" recessed outlet box: 5.625" W., 1.375" ht., 5.625" depth			