

Project:			
Fixture Type:			
Location:			
Contact			

P500239-009 Winslett

Immerse yourself in a home atmosphere primed for relaxation and inspired thinking with the beautiful craftsmanship of this pendant. Savor this fresh take on a classic light choice as your gaze traces a sleek stem that extends down from a round ceiling plate to a beautiful brushed nickel light base. A lightly seeded glass shade adds an unexpected, but welcomed dash of modern personality to this clean, traditional design.

- A lightly seeded glass shade adds an unexpected, but welcomed dash of modern personality to this clean, traditional design.
- Savor this fresh take on a classic light choice as your gaze traces a sleek stem that extends down from a round ceiling plate to a beautiful brushed nickel light base.
- Immerse yourself in a home atmosphere primed for relaxation and inspired thinking with the beautiful craftsmanship of this pendant.
- · Ideal for any foyer, kitchen, or dining room.
- · Perfect for transitional, rustic, farmhouse, and coastal settings.
- · Measures 12-7/8-inch width by 17-1/8-inch height.
- Uses three candelabra base bulbs that are sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Pendants

Finish: Brushed Nickel (Plated) **Construction:** Steel Construction

Glass/Shade: Clear Seeded glass Cylindrical Shade,



Diameter: 12-7/8 in Height: 17-1/8 in

Overall Ht. W/Chain: 91-1/2 in

Clear Seeded glass Cylindrical Shade

Width: 12-7/8 in Height: 13-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Three 60 W max. Candelabra	CULus Dry Location Listed
1/8 IP mounting plate for outlet box included	180" of wire supplied	Base or LED equivalent	1-year Limited Warranty
	120 V	E12 base Phenolic sockets	
6 feet of 9 gauge chain supplied			
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth			